

Project:

Fixture Type:

Location:

Contact:

## P350168-009

## **Inspire**

Harkening back to a simpler time, the Inspire Collection Brushed Nickel Three-Light Semi-Flush Mount's timeless demeanor is sure to become a favorite for generations. A round, off-white linen shade with an etched glass diffuser steals the show and creates a beautiful muted glow. Understated metal accents complement the light fixture as it fosters a casual, friendly atmosphere.

- A round, off-white linen shade with an etched glass diffuser steals the show and creates a beautiful muted glow
- Understated metal accents complement the light fixture as it fosters a casual, friendly atmosphere.
- Harkening back to a simpler time, the semi-flush mount's timeless demeanor is sure to become a favorite for generations.
- · Ideal for any hall, foyer, stairways, or kitchen.
- · Perfect for transitional, modern, and farmhouse settings.
- · Measures 18-inch width by 11-1/2-inch height.
- Uses three medium base bulbs that are sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- $\bullet \ \ \text{Progress Lighting products are designed for exceptional quality, reliability, and functionality.}$

Category: Close-to-Ceiling Finish: Brushed Nickel (Plated) Construction: Steel Construction

Glass/Shade: Off White Linen fabric drum shade, Etched glass Flat Round



Diameter: 18 in Height: 11-1/2 in

Off White Linen fabric drum shade

Width: 17-9/16 in Height: -1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	Prewired	Quantity: Three 60 W max. Medium Base or	CULus Damp Location Listed
Mounting Strap	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.187" W., 1.437" ht., 5.187" depth	120 V	E26 base Porcelain sockets	