## PROGRESS LIGHTING<sup>™</sup>

Project:		
Fixture Type:		
Location:		

Contact:

## P350181-031 Stockbrace

Stockbrace Collection 3-Light Matte Black Clear Glass Farmhouse Flush Mount Ceiling Light

Category: Close-to-Ceiling Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Cone



Length: 12-1/2 in Diameter: 12-1/2 in Height: 10 in

Clear Glass Cone Width: 4-1/2 in Height: 6-7/8 in

		ricigiit. 0 //0 iii	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	6 inches of wire supplied	Quantity: three 60 W max.	cCSAus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 V	E26 base Porcelain Socket	1-year Limited Warranty

Ceiling Pan covers a standard 4" recessed outlet box: 11.06" W., 1" ht., 11.06" depth