

Project:

Fixture Type:

Location:

Contact:

P350214-009 Aiken

Aiken Collection One-Light Brushed Nickel Clear Glass Farmhouse Flush Mount Light

Category: Close-to-Ceiling Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Bowl



Diameter: 9 in Height: 9 in

Clear Glass Bowl Width: 9 in Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling semi-flush	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 5" W., 1.56" ht., 5" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	