

Project:

Fixture Type:

Location:

Contact:

## P350217-31M Eva

Eva Collection One-Light Matte Black Mid-Century Modern Flush Mount Light

Category: Close-to-Ceiling

Finish: Matte Black (Painted) with Brushed Bronze accent

**Construction:** Steel Construction **Glass/Shade:** Matte Black Metal



Shown with G30 globe light bulb

Length: 7-3/8 in Diameter: 7-3/8 in Height: 4-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling flush	6 inches of wire supplied	(1) Medium Base (E26) Lamp Type	cCSAus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.75" W., 0.87" ht., 4.75" depth		Fully dimmable with dimmable bulbs.	