

Project:			
Fixture Type:			
Location:			
Contact:			

## P350218-109 Atwell

Atwell Collection 10" One-Light Mid-Century Modern Brushed Bronze Clear Glass Semi-Flush Mount Light

Category: Close-to-Ceiling Finish: Brushed Bronze (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Round



Width: 12 in Depth: 10 in Height: 9-3/4 in

Clear Glass Round Width: 5-7/8 in Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type G16.5	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 5" W., 0.87" ht., 5" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	