

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P350219-109 Delayne

Delayne Collection Five-Light Mid-Century Modern Brushed Bronze Semi-Flush Mount Light

Category: Close-to-Ceiling
Finish: Brushed Bronze (Plated)
Construction: Steel Construction

Diameter: 16 in (not including lamps)
Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	6 inches of wire supplied	(5) Candelabra Base (E12) Socket	cCSAus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type G16.5	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.75" W., 0.75" ht., 4.31" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	