

Project: \_\_\_\_\_  
 Fixture Type: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Contact: \_\_\_\_\_



**P350219-31M**  
**Delayne**

Delayne Collection Five-Light Mid-Century Modern Matte Black Semi-Flush Mount Light

**Category:** Close-to-Ceiling  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Construction

Diameter: 16 in (not including lamps)  
 Height: 5-5/8 in

| MOUNTING  | ELECTRICAL                | LAMPING   | ADDITIONAL INFORMATION     |
|---|---------------------------|---|----------------------------|
| Ceiling mounted   | 6 inches of wire supplied | (5) Candelabra Base (E12) Socket  | cCSAus Dry Location Listed |
| Mounting plate for outlet box included  | 120 VAC                   | Lamp Type G16.5   | 1-year Limited Warranty    |
| Canopy covers a standard 4" recessed outlet box: 4.75" W., 0.75" ht., 4.31" depth |                           | Incandescent: 60-watt MAX per socket<br>LED: 12.5-watt MAX per socket<br>Fully dimmable with dimmable bulbs |                            |