

Project:

Fixture Type:

Location:

Contact:



Category: Close-to-Ceiling

Finish: Brushed Nickel (Plated) with Grey Washed Oak accent

Construction: Steel Construction



Diameter: 15 in Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Flush	6 inches of wire supplied	(2) Medium Base (E26) Socket	cETLus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 13" W., 0.81" ht., 13" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	