

Project:		
Fixture Type:		
Location:		
Contact:		



P350225-012 Astra

Category: Close-to-Ceiling Finish: Satin Brass (Plated) Construction: Steel Construction

Diameter: 18 in (not including lamps) Height: 5-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Semi-Flush	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4"		Incandescent: 60-watt MAX per	
recessed outlet box: 5" W., 0.87" ht., 5" depth		LED: 12.5-watt MAX per socket	
ne, o dopen		Fully dimmable with dimmable bulbs	