

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P350225-020

Astra

Category: Close-to-Ceiling
Finish: Antique Bronze (Painted)
Construction: Steel Construction



Diameter: 18 in (not including lamps)
 Height: 5-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Semi-Flush	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5" W., 0.87" ht., 5" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	