

Project:

Fixture Type:

Location:

Contact:

## **P350226-163** Singleton

Category: Close-to-Ceiling Finish: Vintage Brass (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Bowl



Diameter: 7-5/8 in Height: 7 in

Clear Glass Bowl Width: 7-5/8 in Height: 4-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Semi-Flush	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 5" W., 0.812" ht., 5" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	