

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

**P350231-009**  
**Gilliam**

Gilliam Collection 13 in. Three-Light Brushed Nickel New Traditional Semi-Flush Mount

**Category:** Close-to-Ceiling  
**Finish:** Brushed Nickel (Plated)  
**Construction:** Steel Construction  
**Glass/Shade:** Clear Glass Curved Panel



Diameter: 13 in  
Height: 12-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	6 inches of wire supplied	(3) Candelabra Base (E12) Socket	cULus Damp Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	