

Project:

Fixture Type:

Location:

Contact:

## P350234-31M Atwell

 $\label{thm:local_action} \mbox{Atwell Collection One-Light Matte Black Mid-Century Modern Semi-Flush Mount}$ 

Category: Close-to-Ceiling Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Round



Diameter: 5-7/8 in Height: 7-7/8 in

Clear Glass Round Width: 5-7/8 in Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type G16.5	1-year Limited Warranty
Canopy covers a standard 4"		Incandescent: 60-watt MAX per	
recessed outlet box: 4.75" W., 0.81" ht., 4.75" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	