PROGRESS

Project:		
Fixture Type:		
Location:		

Contact:

P350235-009 Atwell

Atwell Collection Three-Light Brushed Nickel Mid-Century Modern Semi-Flush Mount

Category: Close-to-Ceiling Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Round



Diameter: 22 in Height: 10-5/8 in

Clear Glass Round Width: 5-7/8 in Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	6 inches of wire supplied	(3) Candelabra Base (E12) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type G16.5	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.75" W., 0.81" ht., 4.75" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	