

Project:

Fixture Type:

Location:

Contact:

P350237-015 Cofield

Cofield Collection 12. in Three-Light Polished Chrome Transitional Flush Mount

Category: Close-to-Ceiling Finish: Polished Chrome (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Cylindrical



Diameter: 12 in Height: 7-3/4 in

Clear Glass Cylindrical

Width: 4 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Ceiling Pan covers a standard 4"		socket	
recessed outlet box: 11" W., 1" ht., 11" depth		LED: 12.5-watt MAX per socket	
·		Fully dimmable with dimmable bulbs	