



Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



## P350239-009 Goodwin

Goodwin Collection 13 in. Two-Light Brushed Nickel Modern Farmhouse Semi-Flush Mount Convertible

**Category:** Close-to-Ceiling  
**Finish:** Brushed Nickel (Plated)  
**Construction:** Steel Construction  
**Glass/Shade:** White Linen Fabric Flat Round, Sand Blasted Glass Flat Round

Diameter: 13 in  
 Height: 9-7/8 in  
 Overall Ht. W/Chain: 38 in

White Linen Fabric Flat Round  
 Width: 13 in  
 Height: 4-7/8 in

Sand Blasted Glass Flat Round  
 Width: 12-1/2 in  
 Height: -1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	3 feet of wire supplied	(2) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
2 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth		Fully dimmable with dimmable bulbs	