

Project:			
Fixture Type:			
Location:			
Contact:			



P350240-196

Breckenridge

Breckenridge Collection Five-Light Aged Bronze Rustic Farmhouse Semi-Flush Mount

Category: Close-to-Ceiling Finish: Aged Bronze (Painted) Construction: Steel Construction

Diameter: 22-1/2 in (Dimensions do not include light bulbs) Height: 7-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	6 inches of wire supplied	(5) Candelabra Base (E12) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 5.12" W., 1" ht., 5.12" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	