

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P350243-31M Laramie

Laramie Collection One-Light Matte Black Rustic Modern Clear Seeded Glass
12" Flush Mount Light

Category: Close-to-Ceiling
Finish: Matte Black (Painted) with Gray Sisal accent
Construction: Steel Construction
Glass/Shade: Clear Seeded Glass Cylindrical



Diameter: 12 in
 Height: 8.5 in

Clear Seeded Glass Cylindrical
 Width: 4 in
 Height: 6-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Flush mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Ceiling Pan covers a standard 4" recessed outlet box: 9.06" W., 1.87" ht., 9.06" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	