

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P350244-31M Saucedo



Saucedo Collection Three-Light Matte Black Modern 14.6" Flush Mount

Category: Close-to-Ceiling

Finish: Matte Black (Painted)

Construction: Steel Construction

Diameter: 14-5/8 in

Height: 5.5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Flush	6 inches of wire supplied	(3) Candelabra Base (E12) Socket	cCSAus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Ceiling Pan covers a standard 4" recessed outlet box: 11.68" W., 0.81" ht., 11.68" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	