

Project:			
Fixture Type:			
Location:			
Contact:			



## P350253-009 Gilliam

Gilliam Collection 12-5/8 in. Two-Light Brushed Nickel New Traditional Flush Mount

Category: Close-to-Ceiling Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Bowl

Diameter: 12-5/8 in Height: 4-3/8 in

Clear Glass Bowl Width: 11-5/8 in Height: 3-9/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	ETL Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19 15 W LED	1-year Limited Warranty
Ceiling Pan covers a standard 4" recessed outlet box: 12.62" W., 0.75" ht., 12.62" depth	Fully dimmable with dimmable bulbs		