

Project:		
Fixture Type:		
Location:		
Contact:		

## P350260-009 Adley

Adley Collection One-Light Brushed Nickel Etched Opal Glass New Traditional Flush Mount Light

Category: Close-to-Ceiling Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Etched Opal Glass Bell



Diameter: 8-5/8 in Height: 7-3/8 in

Etched Opal Glass Bell Width: 8-5/8 in Height: 5-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Flush	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 5" W., 0.81" ht., 5" depth		LED: 12.5-watt MAX per socket	
.,		Fully dimmable with dimmable bulbs	