

Project:

Fixture Type:

Location:

Contact:

## P350263-176 Laurel

Laurel Collection 28 in. Six-Light Gilded Silver Transitional Flush Mount

Category: Close-to-Ceiling

**Finish:** Gilded Silver (Hand Painted) **Construction:** Steel Housing



Diameter: 28 in Height: 14-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Semi-Flush	6 inches of wire supplied	(6) Candelabra Base (E12) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.12" W.,		LED: 12.5-watt MAX per socket	
0.81" ht., 5.12" depth		Fully dimmable with dimmable bulbs.	