

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P350264-163
Hillcrest

Hillcrest Collection 13 in. Four-Light Vintage Brass Transitional Semi-Flush Mount Light

Category: Close-to-Ceiling
Finish: Vintage Brass (Plated)
Construction: Steel Housing
Glass/Shade: Clear Glass Flat Panels



Square: 13 in
Height: 11 in

Clear Glass Flat Panels
Width: 12-3/16 in
Height: 6-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Semi-Flush	6 inches of wire supplied	(4) Candelabra Base (E12) Socket	cULus Damp Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs.	