

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P350268-176 Chevall

Chevall Collection Two-Light 12.62 in. Gilded Silver Modern Organic Flush Mount Light

Category: Close-to-Ceiling

Finish: Gilded Silver (Hand Painted)

Construction: Steel Housing

Glass/Shade: Clear Pressed Glass Flat Square/Rectangular



Diameter: 12-5/8 in
Height: 7-7/8 in

Clear Pressed Glass Flat Square/Rectangular
Width: 2-3/4 in
Height: 4-13/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Semi-Flush	6 inches of wire supplied	(2) Candelabra Base (E12) Socket	cETLus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.81" ht., 5.12" depth		Fully dimmable with dimmable bulbs.	