

Project:

Fixture Type:

Location:

Contact:

P350268-204 Chevall

Chevall Collection Two-Light 12.62 in. Gold Ombre Modern Organic Flush Mount Light

Category: Close-to-Ceiling
Finish: Gold Ombre (Hand Painted)
Construction: Steel Housing

Glass/Shade: Clear Pressed Glass Flat Square/Rectangular



Diameter: 12-5/8 in Height: 7-7/8 in

Clear Pressed Glass Flat Square/Rectangular

Width: 2-3/4 in Height: 4-13/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Semi-Flush	6 inches of wire supplied	(2) Candelabra Base (E12) Socket	cETLus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.12" W.,		LED: 12.5-watt MAX per socket	
0.81" ht., 5.12" depth		Fully dimmable with dimmable bulbs.	