

Project:		
Fixture Type:		
Location:		
Contact:		



## P350269-009

## **Boundary**

Boundary Collection 24 in. Four-Light Brushed Nickel Grey Washed Oak Modern Flush Mount Light

Category: Close-to-Ceiling

Finish: Brushed Nickel (Plated) with Grey Washed Oak accent

Construction: Steel Housing, Solid Wood accent

Diameter: 24 in Height: 9-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cETLus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.12" W.,		LED: 12.5-watt MAX per socket	
0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs.	