

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P350269-31M Boundary

Boundary Collection 24 in. Four-Light Matte Black Roasted Chicory Modern Flush Mount Light

Category: Close-to-Ceiling

Finish: Matte Black (Hand Painted) with Roasted Chicory accent

Construction: Steel Housing, Solid Wood accent

Diameter: 24 in
Height: 9-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cETLus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs.	