

Project:			
Fixture Type:			
Location:			



P350270-197

Pinellas

Contact:

Pinellas Collection 25 in. Four-Light White Plaster Contemporary Flush Mount

Category: Close-to-Ceiling

Finish: White Plaster (Hand Painted)
Construction: Steel Housing

Glass/Shade: Painted Steel Cone Shaped Shade

Diameter: 25 in Height: 10-3/4 in

Overall Ht. W/Stem: 28 in

Painted Steel Cone Shaped Shade

Width: 25-1/8 in Height: 5-7/8 in

Painted Steel Cone Shaped Shade

Width: 10-1/8 in Height: 2-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	6 inches of wire supplied	(4) Medium Base (E26) Socket	cETLus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 40-watt MAX per socket	1-year Limited Warranty
One 6", one 12" lengths of stem included		LED: 10-watt MAX per socket	
Communication of the standard 4"		Fully dimmable with dimmable	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		bulbs.	