

Project:			
Fixture Type:			
Location:			
Contact:			



## P350272-191

## Cornett

Cornett Collection 44.12 in. Three-Light Brushed Gold Contemporary Flush Mount Light

Category: Close-to-Ceiling Finish: Brushed Gold (Plated) Construction: Steel Housing

Glass/Shade: Brushed Gold, Painted White Inside Metal Cone

Diameter: 24 in Height: 7-1/2 in

Brushed Gold, Painted White Inside Metal Cone

Width: 2-1/2 in Height: 3-13/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Semi-Flush	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type 15 W max LED	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth	Fully dimmable with dim bulbs.		