## PROGRESS LIGHTING

Project:

Fixture Type:

Location:

Contact:



Cornett Collection 44.12 in. Three-Light Matte Black Contemporary Flush Mount Light

Category: Close-to-Ceiling Finish: Matte Black (Painted) Construction: Steel Housing Glass/Shade: Matte Black, Painted White Inside Metal Cone



Diameter: 24 in Height: 7-1/2 in

Matte Black, Painted White Inside Metal Cone Width: 2-1/2 in Height: 3-13/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Semi-Flush	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type 15 W max LED	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth		Fully dimmable with dimmable bulbs.	