

## Abide LED

Ceiling Flush Mounted • Damp Location Listed 

### Description:

Abide Collection 5-CCT Integrated LED Brushed Nickel Contemporary 10.24" Small Flush Mount Light

### Specifications:

- White PMMA Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Fixture covers a standard 4" recessed outlet box: 10.24 in W, 0.33 in ht., 10.24 in depth
- 6 in of wire supplied

### Performance:

Number of Modules	1
Input Power	16 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,062/65.6 (LM-79)
CCT	2700 K
	3000 K
	3500 K
	4000 K
	5000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	Meets California Title 24 JA8-2022

# P350274-009-CS



### Dimensions:

Diameter: 10-3/16 in  
 Height: 2-3/4 in

White PMMA Diffuser  
 Diameter: 9-1/4 in  
 Height: 2-1/2 in



# P350274-009-CS

## Dimming Notes:

---

P350274-009-CS is designed to be compatible with many Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron\_DVCL-253P

Leviton\_6672

Leviton\_6674

Legrand\_700W WSCL453PTC

Eaton\_SUL06P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.