

Abide LED

Ceiling Flush Mounted • Damp Location Listed **PROGRESS LED**

Description:

Abide Collection 5-CCT Integrated LED Matte Black Contemporary 14" Medium Flush Mount Light

Specifications:

- White PMMA Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Fixture covers a standard 4" recessed outlet box: 14.02 in W, 0.33 in ht., 14.02 in depth
- 6 in of wire supplied

Performance:

Number of Modules	1
Input Power	19.8 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,383/69.1 (LM-79)
CCT	2700 K
	3000 K
	3500 K
	4000 K
	5000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	Meets California Title 24 JA8-2022

P350275-31M-CS



Dimensions:

Diameter: 14 in
 Height: 2-13/16 in

White PMMA Diffuser
 Diameter: 13.07 in
 Height: 2.58 in



P350275-31M-CS

Dimming Notes:

P350275-31M-CS is designed to be compatible with many ELV/Reverse Phase Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_DVCL-253P

Leviton_6672

Leviton_6674

Legrand_700W WSCL453PTC

Eaton_SUL06P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.