

roject:	
ixture Type:	
Active Type.	
ocation:	
out a str	

# Abide LED

# Ceiling Flush Mounted • Damp Location Listed

# **Description:**

One-Light LED Flush Mount

## **Specifications:**

- · Brushed Nickel (Plated)
- · Steel Housing
- · White PMMA Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Fixture covers a standard 4" recessed outlet box
- 6 in of wire supplied

#### **Performance:**

Input Power	31.5 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,713/86.3 (LM-79)
ССТ	2700 K
	3000 K
	3500 K
	4000 K
	5000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	Meets California Title 24 JA8-2022

# P350277-009-CS






#### **Dimensions:**

Length: 32-1/4 in Depth: 18-1/8 in Height: 4-1/2 in

White PMMA Diffuser Length: 30-13/16 in Width: 16-1/2 in Height: 4-3/16 in





PROGRESS LIGHTING\*

Abide LED

Ceiling Flush Mounted • Damp Location Listed PROGRESS LED

Abide LED

Ceiling Flush Mounted · Damp Location Listed PROGRESS LED

P350277-009-CS

**Photometrics:** 

P350277-009-CS

ELECTRICAL DATAP350277-009-CSInput Voltage120 VACInput Frequency60 HzTHD<25%</td>

EMI/RFI FCC Title 47, Part 15, Class B

Operating Temperature -30 °C to 30 °C

Dimming Yes\*

Over-voltage, over-current, short-circuit protected \*See Dimming Notes for more information

### **Dimming Notes:**

P350277-009-CS is designed to be compatible with many ELV/Reverse Phase Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

# **Dimming Controls:**

Lutron NTELV-300
Lutron DVELV-300P
Lutron DVCL-253P
Lutron Caséta
Leviton 6681
LevitonIPI06-1LZ
Leviton 6672

Leviton6674 Lutron SCL-153P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.