

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____



P350280-205 Allegheny

Four-light Semi-flush

Category: Close-to-Ceiling

Finish: Soft Gold (Painted), surrounding frame is Foundry Gold finish

Construction: Steel Construction

Diameter: 24 in
 Height: 12-1/8 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|---------------------------|---|-----------------------------|
| Ceiling Semi-Flush | 6 inches of wire supplied | (4) Candelabra Base (E12) Socket | cETLus Damp Location Listed |
| Mounting plate for outlet box included | 120 VAC | Lamp Type B10 | 1-year Limited Warranty |
| Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth | | Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs | |