

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

**P350281-009**  
**Gilliam**

Three-Light Close-To-Ceiling

**Category:** Close-to-Ceiling  
**Finish:** Brushed Nickel (Plated)  
**Construction:** Steel Construction  
**Glass/Shade:** Etched White Glass Bowl



Diameter: 16-1/8 in  
Height: 4-3/8 in

Etched White Glass Bowl  
Width: 15 in  
Height: 3-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Semi-Flush	6 inches of wire supplied	(3) Medium Base (E26) Socket	cETLus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Ceiling Pan covers a standard 4" recessed outlet box: 16.12" W., 0.68" ht., 16.12" depth		15 W max LED	
		Fully dimmable with dimmable bulbs	