

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P350284-31M Tosca

Three-light Semi-flush

Category: Close-to-Ceiling
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Faux Alabaster Glass Bowl



Diameter: 18 in
 Height: 9-5/8 in

Faux Alabaster Glass Bowl
 Width: 18 in
 Height: 4-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Semi-Flush	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 7" W., 0.81" ht., 7" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	