

DATE:	TYPE:
NAME:	
PROJECT:	

Incandescent

P3509-20

Wisten

Three-light foyer with etched glass and arching rectangular arms with strap accents.

Category: Hall & Foyer

Finish: Antique Bronze (painted)
Construction: Steel construction

Glass: Etched glass tulip shaped shades



Diameter: 12" Height: 26-13/16"

Overall ht. w/chain: 101-13/16"

Glass: 4" dia. Height: 5-1/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included Six feet 9 gauge chain supplied Canopy covers a standard 4" hexagonal recessed outlet box	Threaded socket ring secures glass Pre-wired 15 feet of wire supplied 120V	Quantity: 3 60W Candelabra Base Candelabra phenolic sockets	UL-CUL Dry location listed 1 year warranty Companion fixtures are available