

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3529-09

Harmony

Three-light semi-flush convertible pendant with summer linen fabric shades, brushed nickel finish and a clean, modern design. Can be mounted stem hung or flush mount.

- Clean, modern design.
- Geometric Frame.
- Summer linen fabric shades.
- Includes one 6", four 12" stems and 6 Links of chain.

Category: Close-to-Ceiling

Finish: Brushed Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Fabric Shade fabric shade, Etched glass diffuser



Diameter: 11-13/16"

Length: 13-3/4"

Height: 10-3/8"

Overall Ht. W/Stem: 76-1/4"

Glass

Width: 11-13/16"

Length: 11-13/16"

Height: 4-1/4"

Glass 2

Width: 11-7/16"

Length: 11-7/16"

Height: 0-1/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Ceiling stem hung with 6 links of chain/semi-flush mounted</p> <p>Mounting strap for outlet box included</p> <p>Six links of 9 gauge chain supplied</p> <p>One 6", four 12" lengths of stem included</p> <p>Canopy covers a standard 4" octagonal recessed outlet box</p> <p>4.75" W., 0.8125" ht., 4.75" depth</p>	<p>Pre-wired</p> <p>120 V</p>	<p>Quantity:</p> <p>Three 75w max. Medium Base</p> <p>E26 base porcelain sockets</p>	<p>UL-CUL Dry location listed</p> <p>1 year warranty</p>