

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3530-09

Harmony

Three-light semi-flush convertible pendant with summer linen fabric shades, brushed nickel finish and a clean, modern design. Can be mounted stem hung or flush mount.

- Clean, modern design.
- Geometric Frame.
- Summer linen fabric shades.
- Includes one 6", four 12" stems and 6 Links of chain.

Category: Close-to-Ceiling

Finish: Brushed Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Fabric Shade fabric shade, Etched glass diffuser



Diameter: 15-1/8"
Length: 16-15/16"
Height: 10-7/16"
Overall Ht. W/Stem: 76-7/16"

Glass

Width: 15-1/8"

Length: 15-1/8"

Height: 4-1/4"

Glass 2

Width: 14-9/16"

Length: 14-9/16"

Height: 0-1/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with 6 links of chain/semi-flush mounted Mounting strap for outlet box included Six links of 9 gauge chain supplied One 6", four 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 4.75" W., 0.8125" ht., 4.75" depth	Pre-wired 10 feet of wire supplied 120 V	Quantity: Three 100w max. Medium Base E26 base porcelain sockets	UL-CUL Dry location listed 1 year warranty