

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3531-137

Harmony

Three-light semi-flush convertible pendant with summer linen fabric shades, natural brass finish and a clean, modern design. Can be mounted stem hung or flush mount.

- Three-light semi-flush convertible pendant with summer linen fabric shades.
- Natural brass finish and a clean, modern design.
- Can be mounted stem hung or flush mount.
- Includes one 6", four 12" stems and 6 links of chain.

Category: Close-to-Ceiling

Finish: Natural Brass (Plated)

Construction: Steel Construction

Glass/Shade: White textured fabric shade, etched glass diffuser



Diameter: 18-1/4"

Length: 20"

Height: 11-1/4"

Overall Ht. W/Stem: 77-1/4"

Glass

Width: 18-1/4"

Length: 18-1/4"

Height: 4-15/16"

Glass 2

Width: 17-1/2"

Length: 17-1/2"

Height: 0-1/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Ceiling stem/ctc mounted</p> <p>Mounting strap for outlet box included</p> <p>Six links of 9 gauge chain supplied</p> <p>One 6", four 12" lengths of stem included</p> <p>Canopy covers a standard 4" octagonal recessed outlet box</p> <p>4.75" W., 0.8125" ht., 4.75" depth</p>	<p>Pre-wired</p> <p>10 feet of wire supplied</p> <p>120 V</p>	<p>Quantity:</p> <p>Three 100w max. Medium Base</p> <p>E26 base porcelain sockets</p>	<p>UL-CUL Damp location listed</p> <p>1 year warranty</p>