

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

## P3557-09

### Harmony

Two-light semi-flush convertible pendant with etched glass, brushed nickel finish in a clean modern design. Can be mounted stem hung or flush mount.

- Two-light semi-flush convertible pendant with etched glass.
- Brushed nickel finish in a clean modern design.
- Can be mounted stem hung or flush mount.
- Includes one 6", four 12" stems and 6 links of chain.

**Category:** Close-to-Ceiling

**Finish:** Brushed Nickel (Plated)

**Construction:** Steel Construction

**Glass/Shade:** Etched Outside, Painted White Inside glass bowl



**Diameter:** 11-13/16"

**Length:** 13-3/4"

**Height:** 10-1/4"

**Overall Ht. W/Stem:** 76-1/4"

Glass

Width: 11-13/16"

Length: 11-13/16"

Height: 4-1/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem/ctc mounted  Mounting strap for outlet box included  Six links of 9 gauge chain supplied  One 6", four 12" lengths of stem included  Canopy covers a standard 4" octagonal recessed outlet box  4.75" W., 0.8125" ht., 4.75" depth	Pre-wired  10 feet of wire supplied  120 V	Quantity:  Two 100w max. Medium Base  E26 base porcelain sockets	UL-CUL Damp location listed  1 year warranty