

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3558-09

Harmony

Three-light semi-flush convertible pendant with etched glass, brushed nickel finish in a clean modern design. Can be mounted stem hung or flush mount.

- Three-light semi-flush convertible pendant with etched glass.
- Brushed nickel finish in a clean modern design.
- Can be mounted stem hung or flush mount.
- Includes one 6", four 12" stems and 6 links of chain.

Category: Close-to-Ceiling

Finish: Brushed Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Etched Outside, Painted White Inside glass bowl



Diameter: 15-1/16"

Length: 17"

Height: 10-7/16"

Overall Ht. W/Stem: 76-7/16"

Glass

Width: 15-1/16"

Length: 15-1/16"

Height: 4-5/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem/ctc mounted Mounting strap for outlet box included Six links of 9 gauge chain supplied One 6", four 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 4.75" W., 0.8125" ht., 4.75" depth	Pre-wired 10 feet of wire supplied 120 V	Quantity: Three 100w max. Medium Base E26 base porcelain sockets	UL-CUL Damp location listed 1 year warranty