

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

P3559-09

Harmony

Three-light semi-flush convertible pendant with etched glass, brushed nickel finish in a clean modern design. Can be mounted stem hung or flush mount.

- Three-light semi-flush convertible pendant with etched glass.
- Brushed nickel finish in a clean modern design.Can be mounted stem hung or flush mount.
- Includes one 6", four 12" stems and 6 links of chain.

Category: Close-to-Ceiling
Finish: Brushed Nickel (Plated)
Construction: Steel Construction

Glass/Shade: Etched Outside, Painted White Inside glass bowl



Diameter: 17-7/8" Length: 20" Height: 11-1/4"

Overall Ht. W/Stem: 77-1/4"

Glass

Width: 17-7/8" Length: 17-7/8" Height: 525"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem/ctc mounted	Pre-wired	Quantity:	UL-CUL Damp location listed
Mounting strap for outlet box included Six links of 9 gauge chain supplied One 6", four 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 4.75" W., 0.8125" ht., 4.75" depth	10 feet of wire supplied 120 V	Three 100w max. Medium Base E26 base porcelain sockets	1 year warranty