

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3587-20

Joy

Gleeful simplicity defines the Joy Collection. Refreshing and fashionable, arcing forms of metal and fluted glass shades are enhanced by a classic Antique Bronze finish. This three-light foyer fixture with a truly transitional style is ideal for a variety of interior spaces, including kitchens, dining areas and living rooms.

Category: Hall & Foyer

Finish: Antique Bronze (painted)

Construction: Steel construction

Glass: Etched light umber glass shades



Diameter: 14-5/8"

Height: 17"

Overall ht. w/chain or stem:
103-3/16"

Glass: 4-1/2" dia.

Height: 4-11/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain or stem mounted Mounting strap for outlet box included Six feet 9 gauge chain supplied Two 6" lengths of stem included Canopy covers a standard 4" hexagonal recessed outlet box	Pre-wired 12 feet of wire supplied 120V	Quantity: 3 60W Candelabra Base Candelabra porcelain sockets	UL-CUL Dry location listed 1 year warranty Companion Bath and Vanity, Chandelier, Hall and Foyer, Pendant, Wall bracket, fixtures are available