

## Portal LED

Flush-Mount Mounted • Damp Location Listed **PROGRESS LED**

### Description:

Portal Collection One-Light 13" LED Flush Mount

### Specifications:

- White Acrylic Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Chassis covers a standard 4" recessed outlet box: 11.9375 in W, 0.375 in ht., 11.9375 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied

### Performance:

Number of Modules	1
Input Power	29 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	2,197/75.8 (LM-82)
Lumens/LPW (Delivered)	875/30.1 (LM-79)
CCT	3000 K
CRI	90+ CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Max. Operating Temp	30 °C
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed


# P3632-1530K9



### Dimensions:

Diameter: 13 in  
 Height: 2-1/2 in

White Acrylic Diffuser  
 Diameter: 12 in  
 Height: 0-1/16 in



# P3632-1530K9

## Dimming Notes:

---

P3632-1530K9 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron\_Nova T NTELV-300

Lutron\_Vierti VTELV-600

Lutron\_Maestro MAELV-600

Lutron\_spacer/system SPSELV-600

Leviton\_Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.