

Bulkheads LED

Wall or Ceiling Mounted • Wet Location Listed **PROGRESS LED**

Description:

One-Light 9-1/2" LED Wall or Ceiling Bulkhead

Specifications:

- White Polycarbonate Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" recessed outlet box: 9.125 in W., 1 in ht., 9.125 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied

Performance:

Number of Modules	1
Input Power	17 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1,211/71.2 (LM-82)
Lumens/LPW (Delivered)	922/54.6 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Max. Operating Temp	30 °C
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed

P3650-3130K9



Dimensions:

Diameter: 9-1/8 in
 Height: 4-11/16 in
 H/CTR: 4-3/4 in

White Polycarbonate Diffuser
 Diameter: 9-3/16 in
 Height: 3-5/8 in



P3650-3130K9

Dimming Notes:

P3650-3130K9 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Nova T NTELV-300

Lutron_Vierti VTELV-600

Lutron_Maestro MAELV-600

Lutron_spacer/system SPSELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.