

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3672-104

Elina

The three-light semi-flush convertible fixture from the Elina Collection spins a traditional classic and modern form by exaggerating its heirloom quality details. The fixture's tall, opal glass, K9 glass orb accents and polished nickel finish create the distinctive silhouette.

- Traditional classic and modern form.
- Tall, trumpeted opal glass.
- K9 glass orb accents and polished nickel finish.
- Includes one 6", four 12" stems and 6 Links of chain.

Category: Close-to-Ceiling

Finish: Polished Nickel (plated)

Construction: Steel Construction

Glass/Shade: Etched Opal glass shade



Diameter: 18"
Height: 13"
Overall Ht. W/Stem: 55"

Glass
Width: 18"

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|--|--|--|---|
| Ceiling stem hung with 6 links of chain/semi-flush mounted Mounting strap for outlet box included Six links of 9 gauge chain supplied One 6", four 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 5.5625" W., 0.875" ht., 5.5625" depth | Pre-wired 10 feet of wire supplied 120 V | Quantity: Three 100w max. Medium Base E26 base porcelain sockets | UL-CUL Dry location listed 1 year warranty |