

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

P3779-20

Bound Beveled Glass

Six-sided foyer fixture with clear, bound beveled glass in an antique bronze finish. Solid brass construction. Perfect for entry ways. Hinged door for easy relamping. Antique Bronze finish.

- Six-sided foyer fixture.
- Clear, bound beveled glass.Hinged panel for ease of relamping.

Category: Hall & Foyer

Finish: Antique Bronze (painted)

Construction: Steel Construction

Glass/Shade: Clear Beveled glass panels



Diameter: 12-1/4" Height: 31-3/4"

Overall Ht. W/Chain: 59"

Glass
Width: 6"
Height: 7"
Height: 13"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included 24 in of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5" W., 1" depth	Pre-wired 156" of wire supplied 120 V	Quantity: Six 60w max. Candelabra Base E12 base sockets	UL-CUL Damp location listed 1 year warranty