

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3788-09

Bedford

One-light foyer fixture with etched alabaster glass from the Bedford Collection features softly diffused alabaster glass shades on a finely crafted frame. Striking metallic finish adds richness and depth to the fixture. The style blends well with today's home fashion and provides the perfect accent to your decor. Chain & ceiling mounts both included.

- Brushed Nickel finish.
- Alabaster glass.
- Presents softly diffused light.
- Finely crafted frame with striking metallic features.

Category: Hall & Foyer

Finish: Brushed Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Etched Alabaster glass



Diameter: 10-1/2"
Height: 15-5/8"
14-5/8" ctc
Overall Ht. W/Chain: 54"

Glass
Width: 8-7/8"
Height: 8-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain/ctc mounted Mounting strap for outlet box included Three feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5.5" W., 1.375" ht.	Pre-wired 15 feet of wire supplied 120 V	Quantity: One 150w max. Medium Base E26 base ceramic socket	UL-CUL Dry location listed 1 year warranty