

TYPE:

DATE:

NAME:

PROJECT:

Incandescent

P3854-20

## **Clifton Heights**

Distinctive, chiseled features and crisp, clean lines are key features in this flush mount. Inspired by a modern interpretation of Craftsman styling, a beautiful etched glass shade takes center stage in this design. The contrast of the antique bronze frame with the bright white shade delivers a dramatic, yet refined effect.

- Inspired by a modern interpretation of Craftsman styling, a beautiful etched glass shade takes center stage in this design.
- The contrast of the antique bronze frame with the bright white shade delivers a dramatic, yet refined effect.
- Distinctive, chiseled features and crisp, clean lines are key features in this flush mount.
- Ideal for any hall, foyer, stairway, or kitchen.
- Perfect for transitional or Craftsman settings.
- Measures 12-1/2-inch width by 6-1/8-inch height.
- Uses one medium base bulb that is sold separately (100w max LED, CFL, halogen, or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

## Category: Close-to-Ceiling

Finish: Antique Bronze (Painted)

## **Construction:** Steel Construction

Glass/Shade: Etched Glass Pyramid

| MOUNTING  | ELECTRICAL                   | LAMPING  | ADDITIONAL INFORMATION      |
|---|------------------------------|--|-----------------------------|
| Ceiling mounted   | Pre-wired                    | Quantity:                                      | cCSAus Damp location listed |
| Mounting Swivel Mounting Strap for outlet box<br>included         | 6" of wire supplied<br>120 V | One 100w max. Medium<br>Base or LED equivalent | 1-year Limited Warranty     |
| Ceiling Pan covers a standard 4" octagonal recessed<br>outlet box |                              | E26 base Porcelain<br>socket                   |                             |
| Ceiling Pan: 12.5" W., 1" ht., 12.5" depth                        |                              |  |                             |

Square: 12-1/2" Height: 6-1/8"

Glass Width: 10-3/16" Height: 3-3/8"